19.04.2024 1 von 1





FireSales Mini-Over Pressure-Trainer

Order number: AU-01860

With the Mini Over Pressure Trainer method and experiment of operation concerning repressive ventilation.

The transparent house has a basement, ground floor, first floor and attic. One part operates as the staircase. Floors can be unlinked and removed to make the building smaller. As a result the trainer is also easy to clean. The over pressure trainer contains a smoke channel. From the outside slides can be opened allowing smoke to flow in to the desired rooms. All rooms can be filled with smoke independently. The windows, doors and dormer windows can be opened. In order to simulate discharges the floors have been fitted with slides. For an even higher reality level a LED seat of fire can be placed inside the residence. The various repressive techniques are exercised and studied with the 2 ventilators.

Supplied with: Smoke generator 5 I smoke fluid LED seat of fire 2 ventilators transport box

dimensions: 60 x 54 x 102 cm

E-Mail info@rescue-tec.de

+49-6482-608900

+49-6482-608920

Tel.:

Fax.:

dimensions built up: 60 x 54 x 172 cm